





Q-LINE



SOLARIUM



IRRIGATION



TREADMILL



SAFETY WALL




WALKER

Lubrication systems

Sublime automatic lubrication system

USD Lubrication System Sublime / Article no. 28-4-05-00100




SOLARIUM

IRRIGATION

TREADMILL

SAFETY WALL

WALKER



Proper lubrication of the rotating parts is essential to reduce failure and increase exerciser life.

An automatic lubrication system intended for automating and centralizing grease lubrication is a solution. The system consists of a hose with couplings and a grease cartridge.


The grease cartridge works without a battery and is adjustable between 1 and 12 months. Depending on the use of the mill, you set the period.

This lubrication system is extremely suitable for exercisers that are mounted in the ridge of the roof. The unit is hung next to the control box and connected by the supplied hose to the ring bearing.

- ✓ Replaceable grease cartridges
- ✓ Low installation costs
- ✓ Compact and reliable
- ✓ 12 months maintenance free
- ✓ Temperature range -15° C to +60°C
- ✓ Multifunctional, indoor and outdoor
- ✓ No chemical waste




Features



SOLARIUM



IRRIGATION



TREADMILL



SAFETY WALL




WALKER

Standard options



USD service pack



SOLARIUM



IRRIGATION



TREADMILL



SAFETY WALL



WALKER

Specifications

Connection

3/8" BU BSPT

Drive system

Battery

Basic material

Plastic

Required working pressure

30-60 bar

Fixings

Mounting bracket

Suited for

Slewing ring

Weight

2 kg

Included

20 mtr hose

IP rating

54

Other

250CC

Time

1,2,3,6,12 months

Transport weight

3 kg

Transport size

38 x 28 x 17 cm

Contact details

Q-Line Equestrian B.V.

Haarbrinksweg 47

7678 RS Geesteren

Tel. +31(0)546212361

info@Q-Line.com

www.q-line.com